

50m2 Small Room Hearing Loop System (tie/desk mic version)

Part No. **PDA103L**



Overview

- Everything you need to create a high quality hearing loop system for a room up to 50m2 (7m x 7m).
- Ideal for small meeting rooms, council chambers, doctors' surgeries, etc.
- PDA103 amplifier includes a 3.5mm microphone input (for connecting the tie/desk mic. supplied), a line level input and an 'outreach' socket.
- Metal compensation control helps improve intelligibility in rooms with high metal content
- Adjustable mic, line level and 'outreach' controls.
- Drive (level) control allows the amplifier's output stage to be set-up to suit the exact characteristics of the application.
- State-of-the-art audio processor features an automatic gain control which compensates for poor microphone techniques and helps suppress loud noises, hisses and clicks.
- Limit, Peak, Loop Fault and Power On indicators,
- Designed to be wall-mounted using the keyholes provided.
- Exceeds the requirements of BS7594 and EN60118-4 when correctly installed.



More Information

Technical Specifications

| | |
|---------------------------|---|
| Type | Wall mountable. Plugtop mains lead supplied. |
| Coverage | 50m2 approx. |
| Mains supply | Plugtop mains lead supplied. Rated supply voltage: 110 to 240Va.c. @ 50/60Hz; Rated power consumption: 18W PSU. |
| Max battery size and type | n/a. |



| | |
|----------------------------------|--|
| Auxiliary inputs | 1 x 3.5mm remote mic. socket; 1 x 3.5mm line level socket; 1 x Outreach socket. |
| Indicators | Limit; Peak; Loop Fault; Power On. |
| Controls | Mic; Line; Outreach; Metal Compensation (all individually adjustable) and Loop Drive (Level). |
| Connections | Mic (3.5mm mono jack socket); Line (3.5mm stereo jack socket); Outreach (4-way pluggable screw terminal; DC in; Loop (2-way pluggable screw terminal). |
| Product dimensions (mm) | W 135 x H 130 x D 35mm (amplifier only); W 340 x H 250 x D 73mm (kit box). |
| Construction & finish | Black metal. |
| IP Rating | IP40. |
| Weight | 380g (amplifier only). 1.15kg (kit box and contents). |
| Operating conditions/temperature | -5°C to +40°C. Max relative humidity: 95%. |
| Kit contents | PDA103 amplifier; PL1/PSU1 plugtop power supply; AMT microphone; 40m loop cable; 'Hearing Loop Fitted' sticker. |



T 01942 322744 E sales@c-tec.co.uk
F 01942 829867 W www.c-tec.com



C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom